

**TECHNICAL SPECIFICATIONS**

<b>Trade Name</b>	Narrow neck bottles - grey
<b>Use</b>	Completely opaque. Excellent for all photosensitive material whether liquid or solid.
<b>Material</b>	Body in Polyethylene (PE); cap in Polypropylene (PP) and undercap in Polyethylene (LDPE)
<b>Other Features</b>	Shoulder and cap with holes for safety seal or identification labels application. Permanent graduation printed in relief externally.

**DIMENSIONAL SPECIFICATIONS**

<b>Height with mounted cap</b>	266,00 mm
<b>External base diameter</b>	112,00 mm
<b>Internal mouth diameter</b>	33,00 mm
<b>General dimensional tolerance</b>	+/- 0,50 mm
<b>Bottle wall thickness</b>	1,00 +/- 0,20 mm
<b>Capacity</b>	2000 ml
<b>Graduated scale</b>	Ogni 100 ml

**GENERAL FEATURES**

<b>CE Mark</b>	No
<b>Foodstuff suitability</b>	Yes according to: EC Regulation 1935/2004
<b>Seal granted by</b>	Quality of both cap and mouth thread, presence of the under cap
<b>Translucence</b>	No. Completely opaque
<b>Temperature range of the bottle</b>	Da -50°C a +80°C

**STERILIZATION OF THE BOTTLE**

<b>Autoclavability + 121°C</b>	No
<b>Gas (Ethylene Oxide)</b>	Yes, without cap and undercap
<b>Dry Heat (+160°C)</b>	No
<b>Chemical (Formalin)</b>	Yes
<b>Irradiation</b>	Yes
<b>Microwave</b>	Yes, without cap and undercap

**Quality Assurance**  
Massimiliano Capitanio**Technical Direction**  
Guido Borona

**CLEANING OPERATIONS**

Slight contamination	Wash with neutral detergent (pH 7)
Consistent contamination	Wash with alkalin detergent (pH up to 12)

**CHEMICAL RESISTANCES (BOTTLE)**

Categories of substances	Reference	Concentrazione %	T. 20° C	T. 40° C	T. 60° C
Inorganic Acid	Sulphuric acid	98	<b>B</b>	<b>B</b>	<b>B</b>
Organic Acid	Benzoic acid	100	<b>A</b>	<b>A</b>	<b>A</b>
Alcohol	Ethanol	100	<b>A</b>	<b>B</b>	<b>B</b>
Aldehydes	Acetaldeyde	100	<b>B</b>	<b>C</b>	-
Inorganic alkali	Isodium hydroxide	50	<b>C</b>	-	-
Organic alkali	Aniline	100	<b>A</b>	<b>B</b>	<b>C</b>
Ketone	Acetone	100	<b>B</b>	<b>C</b>	-
Esther	Ethyl acetate	100	<b>B</b>	<b>C</b>	-
Hydrocarbons, halogenated	Dichloroethylene	100	<b>C</b>	-	-
Hydrocarbons, aromatic	Benzene	100	<b>B</b>	<b>C</b>	-
Hydrocarbons, linear	Hexane	100	<b>C</b>	-	-
Supersolvent	Tetrahydrofuran	100	<b>B</b>	<b>B</b>	<b>C</b>

**Legenda** (not applicable if neglected):

- **A: fair resistance;** exposure (30 days) to the chemical does not cause any damage.
- **B: sufficient resistance;** exposure causes damage of poor importance, which sometimes is only temporary.
- **C: poor resistance;** exposure to chemical is not allowed, or causes immediate permanent damages.

Results of testing with reference materials are to be considered as indication: in case of specific use it is recommended to carry out preliminary testing.

Information about resistance of plastic materials to temperatures, steriization and washing treatments are based on bulletins issued by the Producers of raw materials, on literature data and on the experience gained in using the products

**PACKAGING**

Quantity for each bag	20 pcs with mounted cap and undertap
Quantity in each box	2 x 20 = 40 pcs with mounted cap and undertap

**Quality Assurance**  
Massimiliano Capitanio**Technical Direction**  
Guido Borona